

Lightwave 3 & Lightwave 3+

WPA Spectrophotometers



FEATURES & BENEFITS

- UV/Visible spectrophotometer covering 190 to 1100 nm allows you to see more of your sample
- Save data to a USB flash drive so results can be analysed later
- Builds on the success of the WPA Lightwave range
- PVC (Print Via Computer) software is included and allows you to transfer data directly from the instrument to your PC
- Optional integrated printer and wireless Bluetooth® accessories

The Lightwave 3 and 3+ diode array spectrophotometers offer all the benefits associated with the established WPA Lightwave range. Predefined methods for rapid scanning, kinetics and concentration capabilities, a variable pathlength cell holder up to 40 mm and their compatibility with disposable low volume UV cuvettes have made them a common sight among educational and industrial laboratories alike.



SPECIFICATIONS

Technical

Wavelength Range	190 to 1100 nm
Monochromator	Flat grating
Wavelength Calibration	Automatic upon switch on
Beam Height	15 mm
Spectral Bandwidth	5 nm or 3 nm for '+' models
Wavelength Accuracy	±2 nm
Wavelength Reproducibility	±1 nm
Light Sources	Xenon flash lamp
Detector	Twin CMOS array
Photometric Range	-0.300 to 2.500 A, 0.3 to 199 %T
Photometric Linearity	±1.3 % or ±0.008 A whichever is greater at 546 nm
Photometric Reproducibility	±0.002 A to 0.5 A at 546 nm
Stray Light	<0.5 %T 340 nm
Stability	±0.01 A/h at 340 nm
Noise	±0.005 peak to peak ±0.002 RMS

Software

Applications	Single wavelength Multi wavelength Concentration Standard curve Wavelength scanning Kinetics Absorbance ratio
Digital Output	USB flash drive, PC via PVC software, Optional Bluetooth
Data Export	USB flash drive: .tsv, native PVC format PC via PVC: .csv, .emf, .xlsx, .xls, .rtf, .tsv, native PVC format
Method Storage	90 with PIN number protection
Graphical Display	Yes, zoom and track function
Sample ID	Yes
Languages	English, German, French, Spanish, Italian, Japanese, Chinese
Dimensions	260 × 390 × 100 mm
Weight	3.00 kg

ORDERING INFORMATION

Part Number	Description
80-3007-42	WPA Lightwave 3
80-3007-43	WPA Lightwave 3 with Printer
80-3007-44	WPA Lightwave 3 with Bluetooth
80-3007-45	WPA Lightwave 3 with Printer and Bluetooth
80-3007-47	WPA Lightwave 3+
80-3007-48	WPA Lightwave 3+ with Printer
80-3007-49	WPA Lightwave 3+ with Bluetooth
80-3007-50	WPA Lightwave 3+ with Printer and Bluetooth

For further information, please contact your local Biochrom Sales Representative or Distribution Partner.

CONTACT BIOCHROM



77, avenue de Champagne - 91420 MORANGIS
Tél. : 01 60 19 69 29 - info@bioserv.fr - www.bioserv.fr